



Candling table, type CT-1



The Pas Reform candling table improves hatchability and chick quality. The machine consists of an egg receiving and candling section.

Candling

With the candling table clears (non-fertile eggs) are identified. For that purpose a stainless steel light-conductor has been assembled underneath the machine. In the cover of the lampholder ten holes are fitted, which correspond to the centre of the eggs on one row of the setter tray.

Technical Specifications

Manual candling table, type CT-1: An aluminium lampholder is assembled in a galvanised steel frame. In the stainless steel cover of the lampholder are ten holes which correspond with the centre of the eggs on one row of a setter tray. The setter trays have to be pushed over the table by hand

Dimensions (LxWxH) 1000 x 560 x 1015 mm

Manual candling table with discharge conveyor, type CT-2: Similar to type CT-1. After candling the setter trays have to be pushed over the table onto the discharge conveyor by hand

Dimensions (LxWxH) 3000 x 560 x 1015 mm

In our commitment to quality improvement through continuous research, we reserve the right to alter specifications of our products without notice

