



Candling table, type CT-15



The Pas Reform candling table improves hatchability and chick quality.



Candling

With the candling table clears (non-fertile eggs) are identified. For that purpose a halogen light has been assembled underneath the machine. In the cover of the candling table 150 holes are fitted, which correspond to the centre of the eggs on the setter tray. After positioning of the setter tray the cover is lifted up by means of a handle, to cover the holes with the eggs.

Technical Specifications manual candling table, type CT-15

The setter trays have to be pushed over the table by hand to the conveyor (2 m long).

Materials	The table is constructed of stainless steel and mounted on swivel castor wheels for easy transport
Electrical requirements	230/400 Volts, 50 Hz, 1 Ph + 0 + PE
Power consumption	1 kW
Dimensions	(LxWxH) 760x640x900 mm
Type of setter trays	Pas Reform Standard setter tray, Pas Reform Regular setter tray, Petersime setter tray. For each of these trays another cover can be provided
Options	Supply or Discharge conveyor

In our commitment to quality improvement through continuous research, we reserve the right to alter specifications of our products without notice

